

TYPE APPROVAL CERTIFICATE

This is to certify:**That the Bulk Loading Hoses with Permanently Fitted Couplings**with type designation(s)
Multi-Vapor Yellow

Issued to

Gutteling B.V.
Rotterdam, Zuid-Holland, Netherlands

is found to comply with

DNV GL class programme DNVGL-CP-0183 – Type approval – Flexible hoses**Application :****Product(s) approved by this certificate is/are accepted for installation on vessels classed by DNV GL.****Temperature range: -20°C to +100°C****Max. working press.: 5 bar****Sizes: 2",3",4",6",8",10" (28 mm to 250 mm)**Issued at **Høvik** on **2019-01-30**for **DNV GL**This Certificate is valid until **2023-12-31**.DNV GL local station: **Rotterdam**Approval Engineer: **Adel Samiei**

Marianne Spæren Marveng
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



Job Id: **262.1-011148-8**
Certificate No: **TAP00001F6**

Product description

Flexible hose assemblies with the following constructional features:

Wire reinforced hoses constructed with inner wire of polypropylene coated steel, inner lining of polypropylene fabrics, reinforcements of polypropylene fabrics and films, outer cover of polyester PVC coated fabric and outer wire of galvanized steel with permanently fitted couplings

End connection (to the hose): according to manufacturer's drawing listed in this certificate.

End connection (to ship): Slip-on weld flange, lapped flange, weld neck flange and TTMA fixed flange (according to ASME B16.5 or EN1092-1)

Coupling material: Galvanized steel or stainless steel AISI 316L

Hoses and couplings are manufactured by Gutteling B.V., Rotterdam, Netherlands

Application/Limitation

This certificate is valid for the specific assembly of hose and coupling type as specified, assembled and delivered by the holder (named as manufacturer) of this certificate.

The hoses may be used for transfer of chemicals as per manufacturer's chemical resistance list.

The hoses may be used for temporary filling and discharge only. They are not to be permanently fitted.

The hoses covered by this certificate shall be used in accordance with manufacturer's instruction manual.

The scope of approval does not cover the hose handling device(s) (padeye or lifting lugs, collars, etc.)

Hoses covered by this certificate shall not be subject to vacuum condition during operation.

Production test

Each hose covered by this certificate shall be hydrostatically tested at ambient temperature to a pressure equal to 1.5 times maximum working pressure before being placed in service.

Type Approval documentation

Manufacturer's drawing:

GUT/HOSE/05-102, GUT/HOSE/05-103, GUT/HOSE/05-104/rev01, GUT/HOSE/05-105/rev01

GUT/STUB/01-00, GUT/MALE NIPPLE/01-00, GUT/FERRULE/01-00, GUT/FERRULE/02-00

Leakage test, change in length, twisting test, electrical conductivity and dimensional check test report dated 2006-08-03 witnessed by DNV surveyor.

11432421_a, 1432421_b, 11432421_c, 11432421_e, 11432421_g, 11432421_i dated 2003-09-24 witnessed by DNV surveyor.

Gutteling report No. 080420/SV1 including hose description and condition, test and evaluation results.

Bend test, vacuum test, IBC code test dated 2006-08-03 witnessed by DNV.

IBC code test report dated 2003-09-03/2008-08-21

Renewal test dated 2010-10-13 witnessed by DNV.

Chemical resistance list version 2017-09-20

Renewal burst pressure test report witnessed by DNV GL dated 2018-11-30

Tests carried out

Vacuum test, proof pressure test, impulse test, cold flexibility test, IBC-Code test, oil resistance test, burst test, bend test and change in length test.

Marking of product

Each end fitting shall bear a permanent identification, showing, as a minimum:

- name of manufacturer;
- hose assembly serial number;
- internal diameter of the hose;

The hose shall be permanently marked with:

- the date of the proof pressure testing,
- its specified MAWP,



Job Id: **262.1-011148-8**
Certificate No: **TAP00001F6**

- its maximum and minimum service temperature;

Periodical assessment

For retention of the Type Approval, a DNV GL Surveyor shall perform periodical assessment after two years (+/- 90 days) and after 3.5 years (+/- 90 days) to verify that the conditions for the approval are complied with. Reference is made to DNVGL-CP-0338.