

Guillemín Revolving

CHEMICAL - PETRO-CHEMICAL

TECHNICAL DESCRIPTIONS

Swivel Ears 360°
 Coupling Material = ASTM CF8M/1.4408
 Gasket Material = CSM
 Black locking ring for visual identification of the coupling
 Working pressure = 16 bar
 Max. Working T°C (with CSM gasket) = 120°C

ADVANTAGES

- Avoid torsion of the hose during connection
- Assembly is lighter:
 no swivel coupling M/F added
- Enhanced security compared to coupling without ears

RECOMMENDATIONS

Remove the CSM gasket before welding

COMPLEMENTARY INFORMATIONS

Patent number : P281-B-41739

www.trelleborg.com/fluidhandling

Contact: robin.lallemand@trelleborg.com

STAINLESS STEEL 316

Part number	Size coupling mm	Size shank mm	End fittings	Stock
5105247	DN 50	60,3 mm	Welding end	✓
5105248	DN 80	88,9 mm	Welding end	✓
5105281	DN 100	114,3 mm	Welding end	✓
5105249	DN 50	Helico shank DN 50	For composite hoses DN 50	✓
5105250	DN 80	Helico shank DN 80	For composite hoses DN 80	✓

