



# CHECKER + Checker matting

16/07/2014

**TECHNICAL MATTING:  
HIGH PERFORMANCE**

**FEATURES**

Checked pattern.

**ADVANTAGES**

- High dimensional and color stability
- High hardness and abrasion properties, which means a better transit resistance
- Good scratch resistance
- Good adhesion to different possible substrates
- Non-slippery
- Thermal and acoustic insulation
- Noise, vibration, and cold propagation reduction
- Very good wear and tear resistance
- Excellent walking and standing comfort
- Easy to clean and low maintenance

**BENEFITS**

- Safety
- Comfort
- Economy

**APPLICATIONS**

Suitable for industrial site.

Indoor installations.

Warehouses, aisles, locker rooms, machine or heavy equipment fronts, with no specific chemical or mechanical requirements.

[www.trelleborg.com/elastomerlaminates](http://www.trelleborg.com/elastomerlaminates)

**MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES**

	Measured characteristics	Standard	Value
<b>MECHANICAL</b>			
	<i>Rubber compound</i>		SBR/NR
	<i>Hardness</i>	ASTM D2240	70 ± 5 Shore A
	<i>Abrasion resistance (5 N)</i>	ISO 4649	≤ 200 mm <sup>3</sup>
	<i>Residual indentation</i>	EN ISO 24343	≤ 0.15 mm
	<i>Dimensional stability</i>	EN ISO 23999	± 0.3 %
	<i>Sound insulation</i>	ISO 10140-3	12 dB
<b>CHEMICAL RESISTANCE</b>			
	<i>Common cleaning products</i>	EN 423	<b>Good</b>

**PROFILE**



Checker (MK)

**DIMENSIONS**

Colour	Thickness (mm)	Width (mm)	Length (m)	Weight (kg/m <sup>2</sup> )	Pattern
●	3 ± 0.3	1400 ± 2 %	10 ± 2 %	3.9	MK
●	5 ± 0.3	1400 ± 2 %	10 ± 2 %	6.9	MK

Other colours are available under request

**IDENTIFICATION**

<i>Branding</i>	Without.
<i>Back face</i>	Fabric impression.
<i>Packaging</i>	Rolled on cardboard tube Ø 80 mm.
<i>Wrapping</i>	Black polyethylene film.
<i>Labelling</i>	Self-adhesive label indicating product name, dimensions, area in m <sup>2</sup> , nominal weight, and product code to allow product traceability.