

ADVANTAGE UV STRIPPING JOY

UV COATING BLANKET

BENEFITS:

- Cord carcass for improved dimensional stability
- Optimal for aqueous and UV varnishing
- Clean stencil cutting either manually or CAD-assisted
- Excellent for spot coating
- Longer service life
- Reusable

NEW TECHNOLOGY


Radial cord carcass with a special layer for easy stripping

COLOUR	Apricot
CONSTRUCTION	Cord carcass
TYPE	Compressible
SURFACE HARDNESS	68 +/- 3 IRHD
STRETCH	< 0.70% @ 500 N/5 cm
NOMINAL THICKNESS	1.95 mm (ISO 12636)
BOTTOM LAYER	Water/Solvent sealed
MINIMUM STENCIL DEPTH	0.90 mm (1.95 mm)
PEEL STRENGTH	25 - 40 N/50mm
FACE COMPOUND	For UV and oxidation ink drying systems

MAIN APPLICATION

Sheetfed	●
Packaging	●
Coating	●
Metal decorating	●
Business forms and labels	●
Heatset	●
Coldset	●

● Recommended ● Suitable ● Not recommended



- A** - Printing surface
- B** - Fabric ply
- C** - Closed-cell compressible layer
- D** - Strippable ply
- E** - Cord ply
- F** - Sealed bottom fabric