



Rollin® PFUV


Key performance

- EPDM surface designed for use with UV inks and solvents.
- Specially formulated for maximum sheet release.
- Perfect for stocks and inks that are prone to picking, piling or linting.
- Enlarged compressible layer for increased smash resistance and blanket longevity.

MAIN APPLICATION

Sheetfed, Packaging, Metal Decorating

Rollin PFUV is available in 3 and 4 ply, .067"/.077" thickness.



The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOR	Caribbean Blue
NOMINAL THICKNESS (Inches)	.067" ± .001" (1.71mm ± 0.02) 3 ply/ .077" ± .001" (1.96mm ± 0.02) 4 ply
AVERAGE LOAD VALUE N/cm² @ 0.23 mm INDENTATION	180
SURFACE ROUGHNESS	0,9
ELONGATION (%)	Max. 7
TENSILE STRENGTH (N/MM)	Min. 60
WATER & SOLVENT PROTECTION	No
HARDNESS	78 Shore A
BLANKET CONSTRUCTION	Compressible

FOR ANY FURTHER DETAILS AND FOR A QUOTATION PLEASE REFER TO YOUR SALES MANAGER OR EMAIL US AT: printing@trelleborg.com

www.trelleborg.com/printing

The information contained in this document is intended to provide guidance. The information is NOT a specification and all figures in the document are nominal. This document and the information it contains do not create any warranties for any product and Trelleborg Printing Solutions disclaims any warranty of merchantability or fitness for a particular purpose for the product described in this document. This document discloses information that is proprietary to Trelleborg Printing Solutions. The receipt or possession of the document does not confer any right to reproduce or disclose the document, any information contained in it, or any physical article or device, or to practice any method or process except by written agreement with Trelleborg Printing Solutions. Trelleborg Printing Solutions is committed to the ongoing development of its products. For that reason, Trelleborg Printing Solutions reserves the right to alter the actual specifications of its products without prior notice.