

ADVANTAGE UV Stripping JOY

Coating blanket

Specially designed for UV inks with a stable pre-carcass and optimum compressible layer construction for easy stripping on coating units. Also suitable for printing.

COLOUR
FACE COMPOUND
CONSTRUCTION
TYPE
SURFACE FINISH
MICRO HARDNESS
STRETCH
NOMINAL THICKNESS
MINIMUM STENCIL DEPTH
PEEL STRENGTH
BOTTOM LAYER
PACKING & TENSIONING

Apricot
 For UV and oxidation ink drying systems
 Cord Carcass
 Compressible
 Ground and polished
 68 +/- 3 IRHD
 < 0.70% @ 500 N/5 cm
 1.95 mm (ISO 12636)
 0.90 mm (1.95 mm)
 25 - 40 N/50mm
 Water/Solvent sealed
 Conform to OEM instructions

APPLICATION


- Sheetfed
- Heatset
- Coldset
- Packaging
- Coating
- Metal

VARNISH

- UV
- Aqueous

● Recommended ● Suitable ● Not recommended

STRUCTURE



CHARACTERISTICS

Smoothly polished surface

Exceptionally stable pre-carcass ply

Unique carcass

ADVANTAGES

Offers an even varnish film thickness with minimum pressure settings and optimum varnish transfer.

Calibrated radial cord pre-carcass adds dimensional stability for a precise register and reuse of blanket.

Calibration of each blanket layer ensures deep stencil depth of min. 0,90 mm for cleaner profiles. Excellent flexibility for an easier press mounting. Clean stencil cutting with sharp edges by hand or CAD. Easy peeling for a quick, trouble-free preparation.