

PRIVILEGE

Sheetfed blanket

This textile-based blanket was designed and formulated for an extremely sharp dot reproduction on a wide range of sheetfed presses. It is suitable for all kinds of inks and paper/carton stocks and it assures a long service life.

COLOUR	Blue
CONSTRUCTION TYPE	Textile carcass
SURFACE FINISH	Compressible
MICRO HARDNESS	Ground and polished
STRETCH	65 +/- 3 IRHD
NOMINAL THICKNESS	< 1.2% @ 500 N/5 cm
BLANKET HARDNESS	1.95 (ISO 12636)
TENSILE STRENGTH	1.70 (ISO 12636)
PACKING & TENSIONING	79 Shore A
	> 3500 N/5 cm
	Conform to OEM instructions


APPLICATION

- Sheetfed
- Heatset
- Coldset
- Packaging
- Coating
- Metal
- Continuous F.

INK

- UV
- Conventional
- Hybrid

STRUCTURE



● Recommended ● Suitable ● Not recommended

CHARACTERISTICS

Dimensional Stability

ADVANTAGES

Unique fabric treatment ensures consistent low setting and optimal laydown.

Closed Cell Compressible Layer

New compressible layer coupled with a textile carcass improves durability, offers excellent shock absorption and rapid recovery. Resists solvent penetration, reduces the risk of delamination.

Microground Printing Surface

Specially formulated surface compound ensures optimal ink transfer and enables extra sharp dot reproduction.

Sealed Bottom Layer

Provides added protection against water and chemical penetration.