


Trelleborg CIPP Liners

THE RIGHT SOLUTION FOR EVERY APPLICATION



Trelleborg MainLiner

- For longer, straight CIPP lining
- Available diameters DN 150 - 1600 (6 - 63 inch)
- Appropriate for ambient, hot water and steam cure



Trelleborg ProLiner


- Longitudinal reinforcements for precise length
- Can navigate 45 degree bends
- Appropriate for ambient, hot water and steam cure



Trelleborg MultiFlex Liner

- For multiple bends up to 90°
- Available diameters DN 30 - 100 (1¼ - 4 inch)
- Appropriate for various curing methods, incl. LED/UV (hot water and steam cure possible when used with calibration hose)

Now also
LED/UV



Trelleborg UltraFlex Liner

- For 90 degree bends and up to 2 transitions
- Available diameters DN 100 - 250 (4 - 10 inch)
- Appropriate for ambient, hot water and steam cure

Trelleborg Resins

VARIABLE WORKING AND EFFICIENT CURING TIMES



Trelleborg Epoxy FC15

- 15 min pot time
- Ambient cured, 2 h at 20 °C (68 °F)



Trelleborg Epoxy FC30

- 30 min pot time
- Ambient cured, 4 h at 20 °C (68 °F)



Trelleborg Epoxy HC60

- 60 min pot time
- Hot cured, 60 min at 60 °C (140 °F)
- Steam cured, 30 min at 80 °C (176 °F)



Trelleborg Epoxy HC120/HC120+

- 120 min pot time
- Hot cured, 30 min at 60 °C (140 °F)
- Steam cured, 45 min 80 °C (176 °F)

