

# Rollin® PFUV


## Key performance

- EPDM surface designed for use with UV inks and solvents.
- Specially formulated for maximum sheet release.
- Perfect for stocks and inks that are prone to picking, piling or linting.
- Enlarged compressible layer for increased smash resistance and blanket longevity.

## MAIN APPLICATION

Sheetfed, Packaging,  
Metal Decorating

**Rollin PFUV is available in 3 and 4 ply, .067"/.077" thickness.**



## The product at a glance

<b>INK COMPATIBILITY</b>	UV
<b>PRINTING SURFACE COLOR</b>	Caribbean Blue
<b>NOMINAL THICKNESS (Inches)</b>	.067" ± .001" (1.71mm ± 0.02) 3 ply/ .077" ± .001" (1.96mm ± 0.02) 4 ply
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0.23 mm INDENTATION</b>	180
<b>SURFACE ROUGHNESS</b>	0,9
<b>ELONGATION (%)</b>	Max. 7
<b>TENSILE STRENGTH (N/MM)</b>	Min. 60
<b>WATER &amp; SOLVENT PROTECTION</b>	No
<b>HARDNESS</b>	78 Shore A
<b>BLANKET CONSTRUCTION</b>	Compressible

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printing@trelleborg.com](mailto:printing@trelleborg.com)**