



# DIMENSION


## Key performance

- Ground and polished surface for quick release and sharp dot reproduction.
- Enhanced compressible layer for consistent load value and smash resistance
- Top compound compatible with conventional and hybrid inks
- Pliable carcass for easy installations

## MAIN APPLICATION

Sheetfet, Packaging,  
Metal Decorating

**Vulcan Dimension is available in  
1.96mm thickness.**



**Vulcan Dimension**



## The product at a glance

<b>INK COMPATIBILITY</b>	Conventional
<b>PRINTING SURFACE COLOUR</b>	Blue
<b>NOMINAL THICKNESS (mm)</b>	1.96
<b>AVERAGE LOAD VALUE N/cm<sup>2</sup> @ 0,23 mm Indentation</b>	200
<b>SURFACE ROUGHNESS (Ra micron)</b>	0,8
<b>ELONGATION (%)</b>	Max.7
<b>TENSILE STRENGTHS (N/mm)</b>	Min. 60
<b>WATER &amp; SOLVENT PROTECTION</b>	No

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printing@trelleborg.com](mailto:printing@trelleborg.com)**

[www.trelleborg.com/printing](http://www.trelleborg.com/printing)

The information contained in this document is intended to provide guidance. The information is NOT a specification and all figures in the document are nominal. This document and the information it contains do not create any warranties for any product and Trelleborg Printing Solutions disclaims any warranty of merchantability or fitness for a particular purpose for the product described in this document. This document discloses information that is proprietary to Trelleborg Printing Solutions. The receipt or possession of the document does not confer any right to reproduce or disclose the document, any information contained in it, or any physical article or device, or to practice any method or process except by written agreement with Trelleborg Printing Solutions. Trelleborg Printing Solutions is committed to the ongoing development of its products. For that reason, Trelleborg Printing Solutions reserves the right to alter the actual specifications of its products without prior notice.