


# In-Plant Manhole Vacuum Tester

**The fastest,  
most versatile,  
high volume  
manhole tester**



Trelleborg's completely redesigned In-Plant Manhole Vacuum Tester is made for the manhole producer who needs to quickly and efficiently vacuum test structures prior to shipment.

The Vacuum Tester is the fastest, most versatile, high volume manhole tester available. With a wireless remote, automated test sequence, and dual test stations, one operator can quickly test manhole after manhole without ever getting off the fork truck.

The high capacity vacuum pump of the In-Plant Vacuum Tester quickly draws a vacuum on even the largest structures.

## FEATURES:

The hydraulic cylinder quickly moves the test head and provides compression for sealing the structure for test

The wireless remote control allows an operator to move the test head from station to station, and start the vacuum test cycle without getting off the fork truck

Dual test station allows for continuous vacuum testing

Tests 48 to 72 inch diameter bases, risers, and cones with heights from one to five feet

Automatic "hands-off" test sequence

Large Pass/Fail indicator light

5 hp pump draws a vacuum on even the largest structures in less than a minute

Heavy-duty wheel motor moves the test head from one test station to the other in 16 seconds

Dual V-rail tracks

Meets ASTM 1244 test requirements



**TRELLEBORG**

[WWW.TRELLEBORG.COM/PIPE-SEALS](http://WWW.TRELLEBORG.COM/PIPE-SEALS)