

# vulcan® Graffity Plus


## Key performance

- Excellent half tone reproduction
- Reduced gauge loss
- Implements all benefits of the **Dynatech System**:
  - Better vibration absorption
  - Less gears streaking marks
  - Higher paper smash resistance
  - Blanket consistency
  - Excellent reboundability

## MAIN APPLICATION

Heatset

**Rollin Graffity Plus is available  
in 3-ply, 1.71 mm thickness**



**Rollin Graffity Plus**



## The product at a glance

INK COMPATIBILITY	Hybrid
PRINTING SURFACE COLOUR	Blue
THICKNESS (mm)	1,71
AVERAGE LOAD VALUE N/cm <sup>2</sup> @ 0,23 mm Indentation	250
SURFACE ROUGHNESS (Ra micron)	0,8
ELONGATION (%)	<0,9
TENSILE STRENGTH (N/mm)	>59
FEED FEATURES	Positive
WATER SOLVENT PROTECTION	Yes
NEW TECHNOLOGY	Dynatech
<b>ADDITIONAL INFORMATION</b>	
APPLICATION	Dynatech

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**