

ADVANTAGE DUAL

Blanket for alternating conventional / hybrid / UV inks

Blanket designed for sheetfed printing jobs where mixed ink systems are in use on the same press.

COLOUR
FACE COMPOUND
CONSTRUCTION
TYPE
SURFACE FINISH
MICRO HARDNESS
STRETCH
NOMINAL THICKNESS
BOTTOM LAYER
PACKING & TENSIONING

Indigo
 For UV and oxidation ink drying systems
 Cord Carcass
 Compressible
 Ground and polished
 68 +/- 3 IRHD
 < 0.70% @ 500 N/5 cm
 1.95 mm (ISO 12636)
 Water/Solvent sealed
 Conform to OEM instructions


APPLICATION

- Sheetfed
- Heatset
- Coldset
- Packaging
- Coating
- Metal
- Continuous F.

INK

- UV
- Conventional
- Hybrid

STRUCTURE



● Recommended ● Suitable ● Not recommended

CHARACTERISTICS

ADVANTAGES

Dimensional Stability

Almost no sinking or stretching giving the blanket an exceptional dimensional stability. After mounting no need for further re-tensioning thus leading to a reduced down time.

Closed Cell Compressible Layer

New compressible layer coupled with a radial cord carcass improves durability, offers excellent shock absorption and rapid recovery. Resists solvent penetration, reduces the risk of delamination.

Microground Printing Surface

Specially formulated mix mode surface compound enables excellent ink transfer and dot reproduction on a wide range of paper/carton qualities. High resistance to swelling against non-aggressive UV drying inks and cleaning agents. Recommended for use with daylight fluorescent inks and metal-pigmented inks and for alternating operation with conventional, mineral-oil-based and UV inks.

Sealed Bottom Layer

Provides added protection against water and chemical penetration.