



RESILIENT | **SKS-900**

SOLID PERFORMANCE

PERFORMANCE DEFINED



TIRE LIFE

Trelleborg products guarantee **the best wear** performance in the industry.

This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.



ENERGY SAVING

Trelleborg is the **largest approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption.

This results in **reduced fuel costs** for our customers.



STABILITY

Trelleborg products are designed to have **large footprints** giving a maximum contact area leading to better stability and even tire wear.



COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

PERFORMANCE AGAINST PREMIUM COMPETITOR


TIRE LIFE




ENERGY SAVING



STABILITY



COMFORT



TRELLEBORG SKS-900

The SKS-900 provides a cost effective and practical solution for landscaping, construction, demolition, mining and utility industries. The SKS-900 eliminates downtime caused from flats. The angled tread lug resists stone drilling which leads to chipping and chunking. The SKS-900 is the ideal choice of operators who require maximum productivity.

The SKS-900 is available primarily as a mounted assembly, with Trelleborg designed wheels to provide maximum slip resistance, but can also be purchased separately. To ensure the best performance these tires are left and right specific.



SKS-900

Tire Size	Loc	Rim Width	Tread Depth (in)	Max Width (in)	Tire Outside Diameter (in)	Load Capacity 5 mph (lbs)	Weight (lbs)
31x10x20 (L)	x	7.5	40/32	9.3	30.5	5,240	146.0
31x10x20 (R)	x	7.5	40/32	9.3	30.5	5,240	146.0
33x12x20 (L)	x	7.5	50/32	11.3	32.6	6,780	203.9
33x12x20 (R)	x	7.5	50/32	11.3	32.6	6,780	203.9

SKS-900 Plain

Tire Size	Loc	Rim Width	Max Width (in)	Tire Outside Diameter (in)	Load Capacity 5 mph (lbs)	Weight (lbs)
31x10x20	x	7.5	9.3	30.5	5,240	158.1
33x12x20	x	7.5	11.3	32.6	6,780	224.4