

SLB e-Form

Envelope printing blanket

Sticky back blanket designed for Envelope printing.

COLOUR	Grey
TYPE	Compressible
FACE COMPOUND	Solvent resistant rubber blend
SURFACE FINISH	Ground and polished
HARDNESS	85 Shore A
MICRO HARDNESS	68 +/- 3 IRHD
NOMINAL THICKNESS	0.90 mm 0.95 mm 1.00 mm 1.07 mm
BOTTOM LAYER	Sticky back
THICKNESS TOLERANCE	0,02 mm

APPLICATION


- Sheetfed
- Heatset
- Coldset
- Packaging
- Coating
- Metal
- Countinuous F.
- Envelope

INK

- UV
- Conventional
- Hybrid

● Recommended ● Suitable ● Not recommended

STRUCTURE



CHARACTERISTICS

Compressible layer with reinforcing ply

Specially formulated surface compound

Adhesive ply

ADVANTAGES

Easy trouble-free stencil preparation. Clean, edged, precision cutting, no spider legs.

Offers uniform ink and coating transfer. Can be used with both conventional and UV curing inks.

The blanket can be easily adhered / removed from different substrates, metal cylinder or blanket and easily repositioned after initial mounting. Once tightly clung, it provides excellent stability at high press speeds and resists most press chemicals. No residual adhesive remains on the press cylinder after blanket removal.