

Cable Compounds

Easy strippable semi conductive thermoset shielding, YLS

E8900 is a conductive thermoset compound intended for XLPE and EPR cable with medium to high stripforce. Can be used in both steam cure and dry cure process.

Specifications

E8900 meets the requirements as below, when optimal processing extrusion and end testing procedure are used:

- AEIC CS8
- BS 6622
- IEC 60502-2
- NF C33-223

Typical physical properties:

Property	Test method	Unit	Typical Value
Density at 23 °C	ASTM D1928	g/cm ³	1,17
Hardness Shore A	ASTM D2240	Shore A	85-90
Hot set 200°C, 20 N/cm ²	IEC 60811-507	%	35/5
Moisture	QAHC-10420, (Karl Fischer method)	PPM	< 800
Tensile strength	ASTM D638	MPa	11
Elongation	ASTM D638	%	250
Mooney viscosity ML (1+4) at 121°C	ISO 289	MU	14-22

Typical electrical properties:

Property	Test method	Unit	Typical Value
DC Volume Resistivity of Cable at 23°C	ASTM D257	Ohm cm	< 400
DC Volume Resistivity of Cable at 90°C	ASTM D257	Ohm cm	< 1000
DC Volume Resistivity of Cable at 120°C	ASTM D257	Ohm cm	< 1000

Insulation shield adhesion:


Property	Unit	Typical Value
Stripping angle/speed	180°/(50 mm/min)	
Stripping force, XLPE, 23°C	N/cm	10
Stripping force, EPR, 23°C	N/cm	23-25

Processing conditions

E8900 provides an excellent surface finish when processing conditions are optimised for the actual processing equipment. Actual conditions will vary according to the equipment used, but as a guide we recommend following extrusion conditions:

Desiccant dryer: < 40 °C

Hopper: -



Neck: 100-130 °C

Head: 100-130 °C

Die: 100-130 °C

Screw cooling: - °C

Comments: -

Extruder

Hopper inlet: 40-60 °C

Barrel: 60-110 °C

Delivery

Form: Pellets

Package: 600 kg box

Storage/Handling

The material is packed, secured and sealed fulfilling the stated properties above. The material shall be stored in sealed container and under dry and tempered conditions to obtain sustainable performance.

Safety

At temperatures above 230 °C there is a risk that acetic acid may be formed.

It is recommended to keep process temperature <260 °C.

Safety data sheet is available upon request.

The data sheet should be considered as guidelines, not binding information.

Issue date 2020-11-02. We reserve the right to make changes without prior notification.



WWW. TRELLEBORG.COM/CABLECOMPOUNDS

E-MAIL: cablecompounds@trelleborg.com