



# Balanced Performance

MID-RANGE MATERIALS HANDLING RESILIENT

## ORCA

Orca is designed with one objective: performance at a competitive price. For applications that are not in constant use or that carry a lower load, as standard Orca proves itself as the most cost-effective tyre in its class. Long mileage, low energy consumption and excellent cut resistance all mean that Orca delivers a solid performance at the right price.

Orca tyres are available in the most common sizes in both LOC and NON LOC (nose retaining bead for easy mounting).

### PERFORMANCE DEFINED

#### TYRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tyre life, **additional hours of usage**, reduced downtime and lower maintenance costs.

#### ENERGY SAVING

Trelleborg is a **leading approved tyre manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced fuel costs** for our customers.

#### STABILITY

Trelleborg products are designed to have **large footprints** maximizing the contact area leading to better stability and even tyre wear.

#### COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

# ORCA

Tyre Size	Alternative Size	Rim Size	LOC	Tyre Dimensions [mm]		Load Capacity [kg]		
				Overall Diameter	Section Width	Static	Forklift trucks up to 25 km/h	
							Load Wheel	Steering Wheel
<b>4.00-8</b>		3.00D-8	•	398	94	1100	950	730
<b>15x4½-8</b>	125/75-8	3.00D-8	•	373	110	1210	1040	800
<b>5.00-8</b>		3.00D-8	•	452	114	1650	1415	1090
<b>16x6-8</b>	150/75-8	4.33R-8	•	409	143	1740	1495	1150
<b>18x7-8</b>	180/70-8	4.33R-8	•	445	147	2490	2145	1650
<b>140/55-9</b>	15x5.5-9	4.00E-09	•	380	132	1360	1170	900
<b>6.00-9</b>		4.00E-09	•	520	130	2190	1885	1450
<b>21x8-9</b>	200/75-9	6.00E-09	•	514	180	3200	2755	2120
<b>6.50-10</b>		5.00F-10	•	568	153	2720	2340	1800
<b>200/50-10</b>		6.50F-10	•	450	175	2870	2470	1900
<b>23x9-10</b>	225/75-10	6.50F-10	•	574	187	4000	3445	2650
<b>7.00-12</b>		5.00S-12	•	646	163	3380	2920	2240
<b>23x10-12</b>	250/60-12	8.00G-12	•	570	219	4380	3770	2900
<b>27x10-12</b>	250/75-12	8.00G-12	•	670	235	4530	3900	3000
<b>7.00-15</b>	29x8-15	5.5-15	•	717	162	4115	3545	2725
<b>7.50-15</b>		6.5-15	•	743	186	4530	3900	3000
<b>8.25-15</b>		6.5-15	•	803	192	5510	4750	3650
<b>28x9-15</b>	225/75-15 (8.15-15)	7.0-15	•	680	200	4530	3900	3000
<b>250-15</b>	250/70-15	7.0-15	•	709	206	5510	4750	3650
<b>250-15</b>	250/70-15	7.5-15	•	709	206	5510	4750	3650
<b>300-15</b>	315/70-15	8.0-15	•	807	244	6795	5850	4500
<b>355/65-15</b>	32x12½-15 (350-15)	9.75-15	•	809	260	9060	7800	6000

**SPECIAL COMPOUNDS AVAILABLE**



Non-Marking

**TREAD PATTERNS**



Orca

