



Trelleborg Premia









RESILIENT - HIGH INTENSITY APPLICATIONS

Main Benefits

- Block tread design**
 Large footprint lowers stress and maximizes tire life.
- Wear resistant technology**
 Less downtime and increased value.
- Shock absorbance**
 Tire absorbs shock from obstacles.
- Rim security**
 Rim protection from accidental damage and anti slip bead wires.
- Enhanced stability**
 Faster load positioning and cornering.
- Energy efficiency**
 Low rolling resistance for improved energy efficiency.

Polymer Engineering, Application Expertise

Trelleborg strives to deliver optimum performance for all our customers. We offer problem-solving products in our premium range. Contact our application specialists to learn more about our latest tire solutions.

 STABILITY	 TIRE LIFE	 BATTERY LIFE	 OVERHEATING TIRE
 VIBRATION	 TIRE CRACKING	 EXPLOSION RISK	 TIRE CHUNKING

Special compounds available



Premia

Size	Alternative Size	Rim	Alternative Pattern	Tire type & Compound availability ● STD ■ LOC ▼ BOTH				Product Dimensions [mm]		Load Capacity [kg]		
				Multi Purpose	Non Marking	Electrically Conducting	Chemical Resistant	Overall Diameter	Section Width	Other	Counterbalanced Lift Trucks up to 25 km/h	
										Static	Load Wheel	Steering Wheel
15x4½-8	125/75-8	3.00D-8		▼	▼	▼		380	115	1,210	1,040	800
15x4½-8	125/75-8	3.00D-8	Ribbed	▼	▼			380	115	1,210	1,040	800
5.00-8		3.00D-8		▼	▼	▼		451	121	1,650	1,415	1,090
16x6-8	150/75-8	4.33R-8		▼	▼	●		412	151	1,740	1,495	1,150
18x7-8	180/70-8	4.33R-8		▼	▼	▼		457	146	2,490	2,145	1,650
140/55-9	15x5.5-9	4.00E-9		▼	▼	▼		381	130	1,360	1,170	900
6.00-9		4.00E-9		▼	▼	▼		528	142	2,190	1,885	1,450
21x8-9	200/75-9	6.00E-9		▼	▼	●		516	188	3,200	2,755	2,120
6.50-10		5.00F-10		▼	▼	▼		571	165	2,720	2,340	1,800
200/50-10		6.50F-10		▼	▼	▼		457	194	2,870	2,470	1,900
23x9-10	225/75-10	6.50F-10		▼	▼	▼		583	208	4,000	3,445	2,650
7.00-12		5.00S-12		▼	▼	▼		657	168	3,380	2,920	2,240
23x10-12	250/60-12	8.00G-12		▼	▼			575	230	4,380	3,770	2,900
27x10-12	250/75-12	8.00G-12		▼	▼	●		676	230	4,530	3,900	3,000
7.00-15	29x8-15	5.5-15		▼	▼	●		723	186	4,115	3,545	2,725
8.25-15		6.5-15		▼	▼	▼		813	203	5,510	4,750	3,650
28x9-15	225/75-15 (8.15-15)	7.0-15		▼	▼	●		700	206	4,530	3,900	3,000
250-15	250/70-15	7.0-15		▼	▼	●	■	713	211	5,510	4,745	3,650
250-15	250/70-15	7.5-15		▼	▼			713	211	5,510	4,745	3,650
300-15	315/70-15	8.0-15		▼	▼	▼	■	814	241	6,795	5,850	4,500
355/45-15	28x12½-15	9.75-15		▼	▼			692	287	6,610	5,690	4,375
355/50-15		9.75-15		▼				713	283	6,610	5,690	4,375
355/65-15	32x12½-15 (350-15)	9.75-15		▼	■			818	300	9,060	7,800	6,000



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels



facebook.com/Trelleborgmaterialhandling



Download the App for free



Tire brochure