



The performance you need

EMR SERIES



The performance you need

The EMR, Earthmover Radial Series, from Trelleborg: tires designed to perform.

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability, while multi-surface tread designs deliver control and perfect grip when it's needed the most - whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable drive, maintaining low fuel consumption.

Designed for loaders, dumpers and grader applications, the EMR tires are suitable for open pits and quarries, underground mines, landscaping, haulage as well as general construction applications.

- **Radial all-steel construction**
- **Reinforced carcass**
- **Multi surface tread pattern**
- **Excellent ride comfort**

EMR Series Earthmover Radial Tires



**RADIAL ALL-STEEL
CONSTRUCTION**



**REINFORCED
CARCASS**



**MULTI
SURFACE**



**EXCELLENT RIDE
COMFORT**



**HIGH GRIP
ON SNOW***



EMR 1020

EMR 1025

EMR 1030

EMR 1030V



EMR 1040

EMR 1042

EMR 1045

EMR 1050

*Available with EMR 1025

TRELLEBORG CONSTRUCTION RANGE

EMR SERIES

LOADER/TRANSPORT SERVICE

Tire Size	Tread Pattern Type	Rim Size (permitted)	New		Loaded Static Radius (in)	Rolling Circumference (in)	Tread Depth (32/nds)	Service Description LI/SS	Tire Load Capacity (lbs) at 6 speed(mph)	Tire Pressure (PSI)	Tire Load Capacity (lbs) at 31 speed(mph)	Tire Pressure (PSI)
			Overall Diameter (in)	Section Width (in)								
17.5 R 25	EMR 1020 TL	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	53.1	17.5	23.2	166.7	35	* 176 A2/157 B	15,565	65	9,096	51
	EMR 1030 TL	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	53.1	17.5	23.2	166.7	28	* 176 A2/157 B	15,565	65	9,096	51
20.5 R 25	EMR 1020 TL	17.00/2.0-25 (17.00/1.7-25)	58.8	20.5	25.5	184.2	39	** 193 A2/177 B	25,358	83	16,097	65
	EMR 1030 TL	17.00/2.0-25 (17.00/1.7-25)	58.8	20.5	25.5	184.2	45	** 193 A2/177 B	25,358	83	17,097	65
	EMR 1030V TL	17.00/2.0-25 (17.00/1.7-25)	58.8	20.5	25.3	177.8	45	** 193 A2	25,358	83	-	-
	EMR 1050 TL	17.00/2.0-25 (17.00/1.7-25)	61.0	20.5	27.0	190.9	107	** 193 A2	25,368	83	-	-
23.5 R 25	EMR 1020 TL	19.50/2.5-25	63.7	23.5	27.5	199.5	43	** 201 A2/185 B	31,973	83	20,396	65
	EMR 1030 TL	19.50/2.5-25	63.7	23.5	27.5	199.5	48	** 201 A2/185 B	31,973	83	20,396	65
	EMR 1040 TL	19.50/2.5-25	65.9	23.5	29.0	206.6	76	** 201 A2/185 B	31,973	83	20,396	65
	EMR 1050 TL	19.50/2.5-25	65.9	23.5	29.0	206.6	113	** 201 A2	31,973	83	-	-
26.5 R 25	EMR 1030 TL	22.00/3.0-25	68.8	26.5	29.9	216.2	52	** 209 A2/193 B	40,785	83	25,358	65
	EMR 1040 TL	22.00/3.0-25	70.8	26.5	32.2	222.3	76	** 209 A2/193 B	40,785	83	25,358	65
	EMR 1050 TL	22.00/3.0-25	70.5	26.2	30.9	215.9	122	** 209 A2	40,785	83	-	-
750/65 R 25	EMR 1030 TL	24.00/3.0-25	63.3	29.3	27.0	199.0	55	** 209 A2/190 B	40,785	83	23,373	62
29.5 R 25	EMR 1030 TL	25.00/3.5-25	73.6	29.6	32.5	221.0	54	** 216 A2/200 B	49,383	83	30,870	65
	EMR 1040 TL	25.00/3.5-25	75.6	29.5	32.6	224.4	82	** 216 A2/200 B	49,383	83	30,870	65
	EMR 1042 TL	25.00/3.5-25	73.7	29.5	32.8	220.8	76	** 200 B/216 A2	49,383	83	30,870	65
	EMR 1050 TL	25.00/3.5-25	75.6	29.5	32.8	228.3	138	** 216 A2	49,383	83	-	-
18.00 R 33	EMR 1045 TL	13.00/2.5-33	73.6	19.8	33.5	220.5	68	** 191 B	-	-	24,030	94

GRADER/LOADER SERVICE

Tire Size	Tread Pattern Type	Rim Size (permitted)	New		Loaded Static Radius (in)	Rolling Circumference (in)	Tread Depth (32/nds)	Service Description LI/SS	Tire Load Capacity (lbs) at 25 speed (mph)	Tire Pressure (PSI)	Tire Load Capacity (lbs) at 6 speed (mph)	Tire Pressure (PSI)
			Overall Diameter (in)	Section Width (in)								
14.00 R 24	EMR 1020 TL	8.00TG-24 SDC (10.00VA-24 SDC)	53.9	14.8	24.2	161.4	32	* 153 A8	8,046	54	-	-
	EMR 1025 TL	8.00TG-24 SDC (10.00VA-24 SDC)	54.0	14.8	24.2	161.4	32	* 153 A8	8,046	54	-	-
17.5 R 25	EMR 1025 TL	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	53.1	17.5	24.1	157.8	35	* 153 A8/176A2	15,562	65	8,046	54

*/** - Index of tire strength



TRELLEBORG

WWW.TRELLEBORG.COM/WHEELS