

TIRE SIZE	PROFILE	RIM WIDTH (IN)	OVERALL DIAMETER (IN)	MAX WIDTH (IN)	TREAD WIDTH (IN)	LOAD CAPACITY 10 MPH (LBS)	LOAD CAPACITY 6 MPH (LBS)	WEIGHT (LBS)
10.5 x 4 – 6	RIB	3.25	10.5	4.0	3.1	1,040	1,440	9.3
15 x 4.5 – 8	RIB	3.00	14.8	4.6	4.3	1,450	2,000	26.9
4.00 x 8	RIB	2.50	16.0	4.1	3.5	1,405	1,940	24.5
4.00 x 8	RIB	3.00	16.0	4.1	3.5	1,685	2,320	24.7
4.00 x 8	RIB	3.75	16.1	4.7	4.3	2,105	2,900	24.9
4.00 x 8	M²	3.75	16.1	4.7	4.3	2,105	2,900	25.4
16 x 6 – 8	RIB	4.33	16.2	6.0	5.4	2,300	3,170	35.9
5.00 x 8	M²	3.00	18.1	4.8	4.2	1,935	2,670	38.8
5.00 x 8	RIB	3.00	18.1	4.8	4.2	1,935	2,670	37.9
5.00 x 8	M²	3.75	18.0	6.0	5.4	2,420	3,340	48.1
5.00 x 8	RIB	3.75	18.0	6.0	5.4	2,420	3,340	38.1
18 x 7 – 8	M²	4.33	18.0	6.2	5.3	2,700	3,750	47.4
6.00 x 9	M²	4.00	20.7	5.5	4.9	3,065	4,230	58.9
6.00 x 9	RIB	4.00	20.7	5.5	4.9	3,065	4,230	58.2
21 x 8 – 9	M²	6.00	20.4	7.3	6.3	4,480	6,190	73.6
200/50 – 10	M²	6.50	18.0	7.7	7.1	3,770	5,200	54.9
6.50 x 10	M²	5.00	22.7	6.3	5.4	4,210	5,810	78.5
6.50 x 10	M²	5.50	22.7	6.3	5.4	4,630	6,390	80.0
23 x 9 – 10	M²	6.50	23.0	7.9	7.1	5,450	7,525	105.8
23 x 10 – 12	M²	8.00	23.1	9.4	9.4	6,385	8,820	112.7
7.00 x 12	M²	5.00	25.6	6.8	5.9	4,810	6,640	104.3
7.00 x 12	PLAIN	5.00	25.6	6.8	5.9	4,810	6,640	104.5
27 x 10 – 12	M²	8.00	26.7	9.4	8.6	6,385	8,820	166.7
7.00 x 15	M²	5.50	28.7	7.1	6.4	5,725	7,905	131.0
8.15 x 15	M²	7.00	27.3	8.8	7.8	6,520	9,000	137.2
7.50 x 15	M²	5.50	29.4	7.6	6.5	5,660	8,125	144.8
7.50 x 15	M²	6.50	29.4	7.6	6.5	6,900	9,600	146.8
250 x 15	M²	7.00	28.2	8.8	7.6	6,960	9,615	149.5
250 x 15	M²	7.50	28.2	8.8	7.7	7,460	10,300	149.5
28 x 12.5 – 15	M²	9.75	28.0	11.8	11.9	9,250	12,760	193.4
8.25 x 15	M²	5.50	31.8	8.2	7.2	6,665	9,200	191.4
8.25 x 15	M²	6.50	31.8	8.2	7.2	7,875	10,875	208.8
300 x 15	M²	8.00	32.0	10.1	8.7	9,550	13,190	241.0
32 x 12.5 – 15	M²	9.75	32.1	11.5	11.3	11,405	15,745	279.8
7.50 x 16	M²	5.50	32.0	8.2	7.2	6,240	8,615	150.4
355/50 – 20	PLAIN	10.00	32.8	12.2	11.4	10,520	14,530	267.2
9.00 x 20	M²	6.50	38.5	8.7	7.6	9,560	13,200	280.4
10.00 x 20	M²	6.50	39.6	9.8	8.6	10,010	13,825	344.6
10.00 x 20	M²	8.00	39.9	9.8	8.6	12,320	17,015	353.8
12.00 x 20	M²	8.00	43.0	10.2	8.9	13,475	18,605	443.0
12.00 x 20	PLAIN	8.00	43.0	10.2	9.0	13,475	18,605	459.0
12.00 x 20	M²	8.50	43.0	10.2	8.9	14,310	19,700	446.0
12.00 x 20	PLAIN	10.00	42.9	12.3	11.1	16,840	23,255	552.3
12.00 x 20	M²	10.00	43.2	12.3	11.0	16,840	23,255	539.0

PROFILES



M²



RIB



PLAIN

ADDITIONAL COMPOUNDS

LONG-DISTANCE® NON-MARKING

High performance non-marking compound for use in applications where floor care is essential.

MAN-TOTER™

A softer version of the M², designed for personnel carriers and in-plant utility vehicles.

SPECIAL COMPOUNDS

Our compounding expertise allows us to offer a wide range of compounds. Please contact us for more details.



TRELLEBORG M²
RESILIENT






Total Value of Ownership

We believe the forklift is one of the most important vehicles on earth. We believe that every part fitted to a forklift should enhance performance and safety.

We believe in going further: creating, adding and delivering value and acceleration through products that are better designed and built to perform; and through behaviors and business practices, which add tangible value to customer operations.

Combined, we call this TVO – Total Value of Ownership; choosing Trelleborg products and Trelleborg as a business partner ensures you receive maximum return for your investment.




- CORE PROCESSES**
 - Research & Development
 - Logistics
 - Production
- CORE BEHAVIORS**
 - Excellence
 - Innovation
 - Customer Focus
- PRODUCT DESIGN**
 - Value
 - Productivity
 - Safety

TRELLEBORG M²

Trelleborg M² is a premium, solid, resilient tire designed for demanding materials handling environments. For forklift trucks that are in heavy use or routinely carrying heavy loads, Trelleborg M²'s design and construction ensures maximum performance.

Trelleborg M² resilient tires feature the Pit Stop Line wear indicator. The Pit Stop Line ensures that users get maximum whole-life value from their choice of tire by always replacing them at the right time and being able to keep forklift downtime to a minimum, as well as always knowing that their tires are safe to use.

INDUSTRY-LEADING PERFORMANCE



ALL-SURFACE GRIP
For better performance on uneven surfaces

CHIP AND CHUNKING RESISTANCE
For a long life in harsh environments

WIDE FOOTPRINT
For better stability, tread wear and performance

THE PIT STOP ADVANTAGE



Choosing Pit Stop Line tires ensures that customers always get maximum value by replacing tires at the right time. As the tire tread wears down, a highly visible orange stripe appears on the tire surface indicating approximately 100 hours of tire life remaining. This allows ample time to schedule replacement at your convenience without compromising performance, safety or productivity.



BENEFITS OF PIT STOP LINE TIRES:

- Reduce Spending
- Increase Productivity
- Increase Safety
- Reduce Impact
- Better Planning

