

Sealing Solutions for Robotic Applications



Your Partner for Sealing Technology

Trelleborg Sealing Solutions delivers better performance and overall profitability through the use of pioneering techniques. Our innovation is key to your success.



LEADING SEALING SOLUTION PROVIDER

Trelleborg Sealing Solutions is a leading global supplier of high quality seals, bearings and components, offering an outstandingly comprehensive sealing portfolio - a one-stopshop providing the best in elastomer, thermoplastic, PTFE and composite technologies. Our solutions are featured in virtually every application conceivable within the aerospace, automotive and industrial segments, including robotics.

As a rapidly evolving industry, robotics is led by constantly innovating technologies, and at Trelleborg our philosophy is the same. We can support you in providing a solution for your application needs. Product reliability and customer focus are paramount.

MANUFACTURING CAPABILITIES

Uniquely placed to offer dedicated design and development, Trelleborg Sealing Solutions globally serves, supports and supplies customers through an unrivalled international network.

- · Over 80 facilities worldwide
- More than 20 manufacturing sites
- · Nine strategically positioned materials and development laboratories
- · Internationally linked design and application centers
- · Global manufacturing capabilities allow us to produce sealing solutions to the same specification and quality standards worldwide



EXPERIENCE AUGMENTED REALITY




To fully experience this augmented reality brochure, scan the QR code to download the app from the App Store or Google Play, or download directly by searching for "Trelleborg Sealing Solutions Augmented Reality Library".

- Install and start the app on your device.
- 2 Use your device to scan the AR symbol wherever you find it in the brochure to see films, animations and other interactive features.

Applications by Industry

Trelleborg Sealing Solutions supports the modern and rapidly evolving robotics industry through its engineering resources, materials expertise and local support.





CONSTRUCTION / DISASTER RECOVERY / PROBE ROBOTICS

Trelleborg Sealing Solutions is a leading supplier of advanced sealing solutions for robotics used in areas where humans can't enter easily due to disasters, deep waters or limited spaces. Trelleborg's solutions support accurate movement, are compatible with aggressive media and withstand extreme temperatures.



SURVEILLANCE / HOUSEHOLD / ENTERTAINMENT ROBOTICS

Trelleborg helps improve performance or manufacturing efficiency by providing unique, custom-engineered solutions – suited to individual needs. This may be a flat gasket of any dimension, a rubber-to-metal element or a LSR component with complex geometry that can consolidate a number of products into one.



DRONES / PERSONAL MOBILITY ROBOTICS

Trelleborg Sealing Solutions is capable of contributing to advances in these intelligent markets based on a comprehensive portfolio of products and materials, and over 60 years of experience providing solutions to numerous industries.



ROBOTICS-RELATED COMPONENTS

Trelleborg Sealing Solutions provides components, manufactured with our innovative materials and engineering, as vital parts to improve performance and efficiency in robotics applications.

Where Our Solutions Are Found

Robotics components must support the unit in its daily operations, maintaining performance and reducing downtime. See some examples of how our products contribute to efficiency and reliability in robotics applications.



CASE STORY: TURCON® VARILIP® PDR

Trelleborg Sealing Solutions was approached to recommend a solution to ensure that the motor brake for a robotics application had a reliable Back-up Seal for a Radial Oil Seal. Should the Radial Oil Seal fail, the oil should be retained for 100 hours without leakage.

Operating Requirements:

- Oscillating speeds up to 1,800 RPM (5,000 max)
- · Dry-running and lubricated performance
- High volume production
- Temperature range: -20 °C to +130 °C / -4 °F to +266 °F

Trelleborg's Solutions:

The seal chosen was a Turcon® Varilip® PDR with a cased, single-element design. An engineered sealing lip featured concentric slits and an extra light lip load, manufactured from PTFE. This satisfied all the operating requirements and enabled high volume, cost-effective production. Testing proved over 8,000 hours of effective dry-running time and an additional 100 hours with oil.

Upper Arm Unit and Wrist Unit

Application Requirements:

- Smooth oscillation (low friction) with good sealing performance
- · Reduce wear on mating surface of seal
- · Compact design

Trelleborg's Solutions:

Wide range of rotary seals in different high performance materials, such as Radial Oil Seals, Turcon® Variseal, Forsheda® V-Ring® and Engineered Molded Parts.

Drive Motor Unit and Reduction Gear

Application Requirements:

- · Operation with high input shaft speed
- · Low friction with good sealing performance
- · Compact design (thin seal width)

Trelleborg's Solutions:

Elastomer-based and PTFE lip shaft seals for drive motors and reduction gear units that are subject to high input shaft speeds.



Drive Motor Unit

Application Requirements:

- · Operation with high input shaft speed
- Low friction with good sealing performance
- Compact design (thin seal width)

Trelleborg's Solutions:

Rotary shaft seals and PTFE lip rotary shaft seals allow for lower friction, heat generation, and robust sealing solutions.

Gearbox Cover

Application Requirements:

- · Reduction of parts
- Elimination of contamination associated with groove voids
- Tolerance against lower quality mating surfaces

Trelleborg's Solutions:

Bonded Seals and Engineered Molded Parts can be used as gearbox lids to protect vital components.

Balance Cylinder

Application Requirements:

- · Low friction with good sealing performance
- · Compact design

Trelleborg's Solutions:

A new Zurcon® polyurethane seal with good abrasion resistance, low compression set, high extrusion resistance and a wide operating temperature range.

Base Unit

Application Requirements:

- Good chemical compatibilities to prevent corrosion of the shaft
- · Low friction with good sealing performance
- · Compact design

Trelleborg's Solutions:

A wide range of rotary seal products and a unique shaft repair kit to maintain rotary shaft lip seals without replacing the shaft.

OUR SOLUTIONS FOR PARALLEL-LINK ROBOTS

Top Cover Lid

Application Requirements:

- · Easy assembly
- Reduction of attachment quantity
- · Secure robot horizontally

Trelleborg's Solutions:

A wide range of rubber-to-metal bonded seals and various rubber gaskets.

Parallel Arm Unit

Application Requirements:

- · Smooth movement
- · Low wear
- Dry running

Trelleborg's Solutions:

Bearings from Orkot® materials, which are a range of thermoset composite bearing materials consisting of technical fabrics impregnated with thermosetting resin. Customer-specific elastomer molded products are also available.

Gearbox Installation Part

Application Requirements:

- · Compact design
- · Easy assembly
- Low friction with good sealing performance

Trelleborg's Solutions:

Choice of a variety of static seal products, from elastomer O-Rings to rubber-to-metal bonded seals to meet customer-specific requirements.


Under Cover

Application Requirements:

- Low friction with good sealing performance
- · Low heat generation
- · Compact design

Trelleborg's Solutions:

A selection of dust seals and scrapers to meet customer-specific requirements.



Movable Plate Unit

Application Requirements:

- Compact design with low weight
- · High speed operation
- Low friction with good sealing performance

Trelleborg's Solutions:

Wide range of rotary seals to prevent the ingress of foreign particles, such as dust, water and chemicals.

OUR SOLUTIONS FOR SCARA ROBOTS

Motor/Reducer Installation Part

Application Requirements:

- · Compact design
- · Easy assembly
- Low friction with good sealing performance

Trelleborg's Solutions:

High performance static seals, from elastomer O-Rings to rubber-to-metal bonded seals that meet customer-specific requirements.



Axis 1 & 2

Application Requirements:

- Chemical compatibility
- · Compact design
- Low friction with good sealing performance

Trelleborg's Solutions:

Wide range of rotary seals, from rubber Radial Oil Seals to PTFE-based rotary seals, to meet customer requirements.

OUR SOLUTIONS FOR CARTESIAN ROBOTS

Vertical and Horizontal Motion Unit

Application Requirements:

- · High speed
- · Compact design
- · Low friction with good sealing performance

Trelleborg's Solutions:

A specially designed low friction pneumatic seal comprising a slipper seal and an energizing O-Ring with a smaller installation size requirement.


Drive Motor Unit and Reduction Gear

Application Requirements:

- · Operation with high input shaft speed
- Low friction with good sealing performance
- Compact design (thin seal width)

Trelleborg's Solutions:

Elastomer-based and PTFE lip shaft seals for drive motors and reduction gear units that are subject to high input shaft speeds.



- · Compact design
- · Low friction with good sealing performance
- Accurate movement and positioning

Trelleborg's Solutions:

A selection of pneumatic and dust seals, manufactured from elastomer-based materials, Zurcon® high-performance polyurethane and Turcon® PTFE materials.



Trelleborg offers one of the most extensive ranges of pneumatic, hydraulic, rotary seals and rubber-to-metal gaskets to match the sealing requirements of robotic applications.



e-Catalog

Struggling to find the right product? Quickly and easily find the solutions for your application and request a quote directly. www.tss.trelleborg.com/ecat



HYDRAULIC SEALS

It is challenging to ensure seal life and performance in hydraulic applications. Not only must leak-free operation be achieved, but high pressures, temperatures and transverse forces must be sustained. Highlighted here are four of the most important seals for hydraulic applications within industrial Articulate Robots and Disaster recovery / Probe robots.



Read the Hydraulic Seals catalog: www.tss.trelleborg.com/literature



TURCON® STEPSEAL® 2K

- · High static and dynamic sealing effect
- · High extrusion resistance meets high hardware clearances
- Low friction, high efficiency
- · Stick-slip free
- · High abrasion resistance and operational reliability
- Wide range of application temperatures and good resistance to chemicals
- · Available for all rod diameters up to 2600 mm



TURCON® EXCLUDER 2/5

- · Outstanding sliding properties
- · Stick-slip free
- · Can follow deflections of the piston, rod or plunger
- · Space-saving construction
- · Very good scraping effect against external contaminants, even with firmly adhered dirt. etc.
- · Excellent scraping effect from the inside against residual oil film adhering to the surface of the piston rod
- Good resistance to hydraulic media



ZURCON® U-CUP RU9

- · High extrusion resistance
- · Excellent dynamic and static sealing
- Optimum environmental protection
- Back-pumping ability over the entire pressure range achieved by grooved
- · Can be used as a secondary seal in combination with Zurcon® Buffer Seal
- · Suitable for sealing systems with double-acting scrapers



ZURCON® SCRAPER ASW

- · Simple groove design
- $\boldsymbol{\cdot}$ Very good scraping effect, wear resistant
- $\boldsymbol{\cdot}$ No tilting or twisting in the groove
- · Simple installation
- · Flush fitting with outer surface



ROTARY SEALS

Rotary seals are used in components with oscillating or rotating parts to keep lubrication fluids in place while preventing the ingress of contaminants. Trelleborg Sealing Solutions components are proven to improve the life and long-term performance of your application, demonstrating superior low-friction properties and excellent resistance to wear.



Read the Rotary Seals catalog: www.tss.trelleborg.com/literature



APJ-CASSETTE SEAL

- All the advantages of Rotary Oil Seals, plus the integration of a fine machined stainless steel, pre-lubricated sleeve
- Provides a fully encapsulated sealing system
- Does not require hardening of the shaft or grinding
- Replacement is easy and fast as the shaft is not worn down by the sealing lip
- · Ideal for robotic motion



SPECIAL ROTARY OIL SEAL

- The advantages of Rotary
 Oil Seals and V-Rings® are both combined in this special design
- Design and materials optimized for robotic motion, offering low torque and low wear
- Design of the axial excluder lip can be tailored according to rotating speed and axial play
- · Ideal for robotic motion



ROTARY OIL SEAL

- High resistance to wear from tailored materials and design
- · Low friction and compression set
- Fluoropolymers available for compatibility with syntetic oils
- Single or double dust lip, according to contamination level and type



FORSHEDA® V-RING®

- Frictional losses and heat kept to a minimum
- Low contact pressure allows dry running in many applications
- · Excellent wear characteristics
- Can perform even with certain amounts of run out, eccentricity and shaft misalignment
- Can be installed over various other components without dismantling





HYBRID ROTARY OIL SEAL

- The advantages of elastomeric Rotary Oil Seals and a Turcon® excluder are combined in this special design
- The tailored elastomeric seal provides the best oil sealing capability, being optimized for
- robotic motion and able to withstand pressure with high eccentricity and vibrations
- The Turcon® lip acts as a back-up excluder against ingress of any sort of chemical aggressive contaminants



TURCON® ROTO VARISEAL®

- Highly abrasion resistant PTFE grades utilizing Trelleborg's material compounding expertise
- Compatible with virtually all fluids, chemicals and gases
- Suitable for reciprocating and rotary applications
- Long service life, good scraping ability even with high viscosity media
- FDA-compliant grades available





TURCON® VARILIP® PDR ROTARY SHAFT SEAL

- Highly abrasion resistant PTFE grades utilizing Trelleborg's material compounding expertise
- Low friction designs with excellent fluid compatibility characteristics and dry running capabilities
- Suitable for high speed shaft applications (up to 100m/s in service)
- · FDA-compliant grades available
- Multiple lip designs available to suit application and contamination levels
- Conductive PTFE grades available to provide electrical discharge



PNEUMATIC SEALS

Pneumatic seals operate in dynamic applications, often at high speeds and generally with reciprocating motions. Trelleborg Sealing Solutions supplies a number of seals, wear rings and scrapers / wipers specifically engineered for pneumatic applications, where cylinders and valves are actuated by air. In addition, where a standard product type is not suitable, custom solutions can be developed.



Read the Pneumatic Seals catalog: www.tss.trelleborg.com/literature



GLYD RING® FOR PISTONS AND RODS

- · Low stick-slip
- · High speed performance
- · Wide range of application temperatures
- · Available for all rod diameters up to 2700 mm



ROD SEAL AND ROD SEAL -SCRAPER COMBINATION

- · For closed and open housings
- · High abrasion resistance and low friction
- · Cost-effective performance
- · Recommended for standard cylinders with a separate scraper, or as a seal/ scraper combination for dry air.



FOR PISTONS AND RODS

- · Good price/performance ratio
- High compressive strength
- Very good sliding effect in dry conditions
- Good resistance to abrasion
- · Low stick-slip effect
- · Simple installation in closed grooves
- · Long life



SCRAPER / **SCRAPER FOR GUIDING UNITS**

- · Excellent chemical resistance
- · Outstanding resistance to heat and low temperature
- · Good resistance to ozone and weathering
- · High resistance to wear
- · Low friction and compression set
- · Highly elastic



ENGINEERED MOLDED PARTS

Trelleborg Sealing Solutions offers one of the broadest ranges of sealing elements on the market. Most of the time, the tried and tested method works, but sometimes a unique application requires a unique solution. Our team of engineers will support you in the development of a customized engineered molded part designed to suit your individual needs. This may be a flat gasket of any dimension, a rubber-to-metal element or a seal

of complex geometry that may consolidate a number of products into one.



Read the Engineered Molded Parts brochure www.tss.trelleborg.com/literature



RUBBER-TO-METAL BONDED SEALS

Embedding seals in a metal plate eliminates the need for making grooves in the counterparts, reducing the manufacturing complexity and associated costs.

Combining several seals into one sealing plate offers several benefits:

- · Easy to assemble
- · Single sealing component reduces
- · Risk of misassembly eliminated, as all seals held in single, visible plate



APPLICATION DESIGN ENGINEERING AND ELASTOMERS COMPOUNDING

- Size range: 20mm 2400 x 900mm
- · Thickness: 0.6mm 10mm
- $\boldsymbol{\cdot}$ Compounds: HNBR, FKM, NBR, EPDM, CR, NR, VMQ, ACM & AEM
- · Materials: Aluminium, Steel, Stainless steel. Engineered plastics
- · Plating/Coating: Corrosion protective plating on steel available, as well as MaxWax® assembly wax treatment

BEARINGS & BUSHINGS

Trelleborg Sealing Solutions is an expert, not just in seals, but in bearings too. In many cases, the use of plastics as the primary bearing material can give distinct advantages.

Plastics offer the user design flexibility and superior performance capabilities, such as lighter weight components, noise reduction and lubrication-free use.



Read the Orkot® Bearings

Engineering Manual for

industrial applications:

www.tss.trelleborg.com/

ORKOT® BEARINGS

Orkot® is a composite consisting of technical fabrics impregnated with thermosetting resins, evenly dispersed solid lubricants and other additives. Orkot® bearings offer significant advantages over traditional metal bearings

- · Self lubricating, environmentally-friendly
- Bespoke sizes and designs possible to optimize performance
- High load capacity and resistant against shocks and vibration
- · Dry or lubricated operation to suit any robotic application
- · Low friction and excellent wear resistance to provide smooth operation between extended maintenance intervals



HIMOD® SLYDRING®

HiMod® Slydring® are made from special, modified thermoplastic material for hydraulic cylinders with medium to high loads.

HiMod® HM0610: A special glass fiber reinforced polyacetal.

- · Velocity, reciprocating: Max. 0.8 m/s
- · Temperature: -40 °C to +110 °C
- · Radial Slydring® pressure: Max. 40 N/mm² at 25 °C and max. 25 N/mm2 at >60 °C

HiMod® HM062: A special glass fiber reinforced heat-stabilized polyamide with PTFE filler.

- · Velocity, reciprocating: Max. 1.0 m/s
- Temperature: -40 °C to +130 °C
- · Radial Slydring® pressure: Max. 75 N/mm² at 60 °C and max. 25 N/mm2 >60 °C



DUROBAL®

Durobal® bearings are used in a variety of devices and equipment where conventional metal bearings can not be used. The inner and outer rings provide support against the mating hardware, while the cage maintains ball separation.



- · Molded to consolidate component parts
- · Materials compatible with virtually all media, both system and cleaning
- Light-weight with good strength and




ORKOT® SLYDRING®

Orkot® Slydring® are wear rings manufactured from tubular or strip composite material. They cover a temperature range from cryogenic to +250 °C in a wide range of media to suit most robotic applications.



- · Eliminates local stress concentrations
- · Wear-resistant, long service life
- · Favorable friction behavior
- · Damping of mechanical vibrations
- · Good wiping effect, embedding of foreign particles possible
- · Simple groove design, easy installation





Unrivaled Littles

Trelleborg Sealing Solutions contributes more benefits than a simple seal supplier. Engineering, design and development teams work with customers across the globe to help them achieve their goals, whether starting from a 'black box' specification, or aiding testing and qualification to get a product to market.



LUBRICATION MANAGEMENT

- Optimized performance
- · Improved friction characteristics
- · Extended system life



PROJECT MANAGEMENT & QUALIFICATION

Full service project management from development to serial production and product introduction

MANUFACTURING & MATERIAL DEVELOPMENT

State-of-the-art development laboratories and manufacturing techniques lead to products with:

- Enhanced chemical compatibility
- Expanded temperature capability
- Reduced weight



- Modern CAD tools (CATIA V)
- · Experienced designers
- · On-site design at customer facilities
- · Dedicated project management
- FEA modeling
- Prototyping
- · Custom-made solutions

TESTING

- Nine research and development centers globally
- World class material & product testing equipment
- Analytical laboratories


MATERIAL EXPERTISE

Trelleborg Sealing Solutions has developed an industry leading group of materials within each material type. Robotics manufacturers can select the compound that best suits their needs.

TURCON®

Turcon® is the brand name of the Trelleborg Sealing Solutions range of proprietary materials based on premium-grade Polytetrafluoroethylene (PTFE). The materials demonstrate low friction, with minimized wear in dynamic and even high speed applications. They are compatible with virtually all media, even at elevated temperatures, and are resistant to aging.

Turcon® M12, is a costeffective material that
provides customers with
extended seal life, as well
as a wide operating window
in terms of temperature,
pressure and velocity.
It performs as well or
better than other
specialized compounds
in each parameter.




ZURCON®

Zurcon® engineered polyurethane-based materials exhibit outstanding friction characteristics. The newly developed Zurcon® Z13 material is specially developed to cope with pressures up to 50 MPa / 7,250 psi at both sides of the seal and at temperatures up to +120 °C / +248 °F.

Chemical Compatibiliy

	Fluid Type	DIN / ISO code	Temperature		Results
	Mineral Oils	HLP/HVLP/HLPD	+110 °C	+230 °F	Excellent
	Synthetic fluids	HEES	+80 °C to +100 °C	+176 °F to +212 °F	Excellent
		HEPG (PAG)	+60 °C	+140 °F	Good
		HEPR (PAO)	+100 °C	+212 °F	Excellent
	Water-based fluids	HFA	+50 °C to +60 °C	+122 °F to +140 °F	Good
		HFC	+60 °C	+140 °F	Excellent
	Synthetic water-free fluids	HFDU	+100 °C	+212 °F	Excellent



ADVANCED ELASTOMER MATERIALS

NBR (Nitrile Butadiene Rubber)

NBR is primarily used with mineralbased oils and greases, providing good mechanical and temperature resistance.

HNBR (Hydrogenated Nitrile Butadiene Rubber)

HNBR is often used in hightemperature applications and demonstrates excellent abrasion resistance and mechanical properties.

FKM (Fluoroelastomer)

FKM is known for its non-flammability, low gas permeability and excellent resistance to ozone, weathering and aging. Suitably formulated FKM can be used down to -35 °C / -31 °F and meets requirements for mineral based oils and greases at high temperatures.

VMQ (Silicone Rubber)

VMQ has very good heat resistance, low temperature flexibility and electrical properties, and excellent resistance to weather, ozone and UV rays. Specific VMQ formulations are resistant to aliphatic engine and gear box oils, water up to +100 °C / +212 °F and high molecular chlorinated hydrocarbons (e.g. Chlophen).

Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Its innovative solutions accelerate performance for customers in a sustainable way.

Trelleborg Sealing Solutions is a leading developer, manufacturer and supplier of precision seals, bearings and custom-molded polymer components. It focuses on meeting the most demanding needs of aerospace, automotive and general industrial customers with innovative solutions.

WWW.TSS.TRELLEBORG.COM









